

RoHS



本产品符合我司QA-3-04-005
环境管理物质标准规范

包装图




Applicable Product No.	2024AF-2*XXX-PTXX-X
适用产品料号	2024AF-2*XXAX/2*XXBX-PTXX-X


Poles Pin位	Pcs/Tray Pcs/盘	Tray/Carton 盘/箱 A3	Pcs/Carton Pcs/箱 A3
2*02	231	18	4158
2*03	198	18	3564
2*04	176	18	3168
2*05	165	18	2970
2*06	143	18	2574
2*07	132	18	2376
2*08	121	18	2178
2*09	110	18	1980
2*10	99	18	1782
2*11	99	18	1782
2*12	88	18	1584
2*13	88	18	1584
2*14	77	18	1386
2*15	77	18	1386
2*16	77	18	1386
2*17	66	18	1188
2*18	66	18	1188
2*19	66	18	1188
2*20	55	18	990



The upper and lower disks must
be stacked in reverse order
上下两盘需反向堆叠




Partial enlarged detail局部放大图A
Scale比例 5 : 1




Partial enlarged detail局部放大图B
Scale比例 5 : 1

步骤步骤1:



步骤步骤2:



步骤步骤3:

Packing step包装步骤:

Step 1: Place the inspected product, arrange neatly and in the same direction into the uptake plastic tray, the quantity cannot be reduced.

步骤1: 将检验好的良品, 整齐并方向一致地摆放入吸塑盘, 不可少数。

Specification of the uptake plastic tray: 2024SP-3400*3400*161

吸塑盘规格: 2024SP-3400*3400*161

Step 2: Overlap the uptake plastic tray, When it overlaps, adjacent upper and lower tray need to be rotated 180 degrees for stacking, one empty uptake plastic tray is stacked together in every 18 products, and put one on the top layer as well, fold them up into a bundle, then cross and parallel wrap with PE film.

步骤2: 将吸塑盘重叠, 在重叠吸塑盘时, 相邻上下两盘需要旋转180度堆叠, 每18盘产品加取顶层放1PCS空吸塑盘叠起来为1扎, 然后用PE膜井字型缠绕。

Step 3: One bundle per carton, put it flat into the carton, then seal the carton with transparent tape, attach outer carton label.

步骤3: 每1扎为一箱, 平整地放入外箱内, 然后用透明胶带封箱, 贴外箱标签。

Note: when the carton is not full, filling material is required, cannot shake too much.

注: 不满箱时, 需使用填充物, 不可晃动太大

Carton size: CB-350*350*260KK A3

纸箱规格: CB-350*350*260KK

Carton material: K=K; Carton thickness: 6~7mm

纸箱材质: K=K; 纸箱厚度: 6~7mm

20240226	A3	EN20240226007	Change carton height, total quantity per carton 变更纸箱高度, 一箱总数量	Tim Teng 滕敏	Larry Yang 杨蒙	一般公差
20230707	A2	ER120230707002	The packaging quantity of 2*10, 2*20Pin is changed according to the actual packaging quantity 按实际包装变更2*10, 2*20Pin的包装数量	Tim Teng 滕敏	Larry Yang 杨蒙	.X ±0.35
20221013	A1	/	Added 2*13Pin-2*20Pin packaging specifications 增加2*13Pin-2*20Pin包装规格	Tim Teng 滕敏	Lyon Zou 邹洪	.XX ±0.25
日期	版次	变更编号	变更内容说明	变更人	核准	.XXX ±0.15
						X: ±2
						视角




SMS 东莞市思索技术股份有限公司
Dongguan SESO Technology Co., Ltd.

料号:	PK-2024AF-2*XXX-PTXX-X
名称:	2.0 mm Female Housing Sub-Assy Packing
单位:	mm
比例:	1:1
页次:	1/1
版本:	A3
编号:	A-000


RoHS

本产品符合我司QA-3-04-005
环境管理物质标准规范


包装图

The upper and lower disks must
be stacked in reverse order
上下两盘需反向堆叠Partial enlarged detail局部放大图A
Scale比例 5 : 1Partial enlarged detail局部放大图B
Scale比例 5 : 1

步骤1:



步骤2:



步骤3:

Applicable Product No. 适用产品料号	2024AM-2*XXX-PTXX-X
----------------------------------	---------------------

Poles Pin位	Pcs/Tray Pcs/盘	Tray/Carton 盘/箱 A4	Pcs/Carton Pcs/箱 A4
2*02	867	21	18207
2*03	646	21	13566
2*04	510	21	10710
2*05	425	21	8925
2*06	357	21	7497
2*07	323	21	6783
2*08	289	21	6069
2*09	255	21	5355
2*10	221	21	4641
2*11	204	21	4284
2*12	187	21	3927
2*13	170	21	3570
2*14	170	21	3570
2*15	153	21	3213
2*16	153	21	3213
2*17	136	21	2856
2*18	136	21	2856
2*19	119	21	2499
2*20	119	21	2499

Packing step包装步骤:

Step 1: Place the inspected product, arrange neatly and in the same direction into the uptake plastic tray, the quantity cannot be reduced.

步骤1: 将检验好的良品, 整齐并方向一致地摆放入吸塑盘, 不可少数。

Specification of the uptake plastic tray: 2024SP-3400*3400*144

吸塑盘规格: 2024SP-3400*3400*144

Step 2: Overlap the uptake plastic tray, when it overlaps, adjacent upper and lower tray need to be rotated 180 degrees for stacking, one empty uptake plastic tray is stacked together in every 21 products, and put one on the top layer as well, fold them up into a bundle, then cross and parallel wrap with PE film.

步骤2: 将吸塑盘重叠, 在重叠吸塑盘时, 相邻上下两盘需要旋转180度重叠, 每21盘产品加取顶层放1PCS空吸塑盘叠起来为1扎, 然后用PE膜井字型缠绕。

Step 3: One bundle per carton, put it flat into the carton, then seal the carton with transparent tape, attach outer carton label.

步骤3: 每1扎为一箱, 平整地放入外箱内, 然后用透明胶带封箱, 贴上下箱标签。

Note: when the carton is not full, filling material is required, cannot shake too much.

注: 不满箱时, 需使用填充物, 不可晃动太大。

Carton size: CB-350*350*260KK A4

纸箱规格: CB-350*350*260KK

Carton material: K=K; Carton thickness: 6~7mm

纸箱材质: K=K; 纸箱厚度: 6~7mm

20240226	A4	EN20240226007	Change carton height, total quantity per carton 变更纸箱高度、一箱总数量	Tim Teng 滕敏	Larry Yang 杨蒙	一般公差	SMS 东莞市思索技术股份有限公司 Dongguan SESO Technology Co., Ltd.				料号: PK-2024AM-2*XXX-PTXX-X			
20220917	A3	ER120220917001	The packaging quantity of 2*10, 2*13PIN is changed according to the actual packaging 按实际包装变更2*10、2*13PIN的包装数量	Tim Teng 滕敏	Lyon Zou 邹洪	.X ±0.35					名称: 2.0 mm Male Housing Sub-Assy Packing			
20220521	A2	EN120220523001	The packaging quantity of 2*06PIN is changed according to the actual packaging 按实际包装变更2*06PIN的包装数量	Tim Teng 滕敏	Lyon Zou 邹洪	.XX ±0.25					单位: 比例: 页次: 版本: 编号			
20220521	A2	EN120220523001	The packaging quantity of 2*06PIN is changed according to the actual packaging 按实际包装变更2*06PIN的包装数量	Tim Teng 滕敏	Lyon Zou 邹洪	.XXX ±0.15					mm 1:1 1/1 A4 A-000			
日期	版次	变更编号	变更内容说明	变更人	核准	视角	核准	审查	制作	日期	杨蒙 刘中华 滕敏 2022/03/11			

RoHS

本产品符合我司QA-3-04-005
环境管理物质标准规范

包装图

Note注解:

1.Quantity数量:

5K PCS/REEL 一卷5KPCS ; 12 REEL/BOX 一箱12卷 ; 60K PCS/BOX 一箱60KPCS A2

2.Each reel and outer box must be labeled and Eco-Label Respectively labeled

每盘和外箱都必须有标签及环保标签分别标示

3.Terminal winding direction as shown端子缠绕方向如左图所示

4.There shall be no dirt such as deformation phenomenon,Mantissa box fillers must be used

每箱不可有脏污,变形现象,尾数箱必须用填充物

5.Cartan material:K=K, Cartan thickness:6~7mm纸箱材质:K=K, 纸箱厚度:6~7mm

6.The paper tape shall be white paper tape with adhesive film and moisture proof

纸带需使用带胶膜防潮白色纸带




7.One waterproof bag, two packets of desiccant 10g and four triangle guard plates should be placed in each carton

每箱里面要放一个防水袋和两包干燥剂10g及四个三角护板


8.Up and down "工" type sealing form上下“工”字型封箱形式

9.Storage conditions: Temperature 10~30 °C;Humidity 20%~65%RH

存储条件: 温度10~30℃; 湿度20%~65%RH

White Tape over the terminal
白色纸带在端子上方The terminal material
belt is downward
端子料带朝下卷装方式
Package wayLabel face up
标签面朝上Waterproof bag防水袋
Drier干燥剂放两包共10gFour paper edge boards
四周放四个护角

Applicable Product No. 适用产品料号	2024TXF-HSN1
	2024TXF-HY2B-X
	2024TXF-HY2B-AX
	2024TXF-HG1-X

Label unified on the
box top right corner
外箱标签位于右上角

20221123	A2	20221123006	依实际变更包装纸箱规格及数量	滕敏	杨蒙	SMS 东莞市思索技术股份有限公司 Dongguan SESO Technology Co.,Ltd. 核 准 审 查 制 作 日 期 杨蒙 张亚会 滕敏 2022/03/11				料 号：PK-2024TXF-HXX-X				
20220521	A1	/	取消纸盘SWB LOGO印字	滕敏	邹洪					名 称：2.00mm Terminal Packing				
20220311	A0	/	首次发行	/	邹洪					单位 比例 页次 版本 编号				
日期	版次	变更编号	变更内容说明	变更人	核 准					mm 1:1 1/1 A2 A-XXX				

RoHS

本产品符合我司QA-3-04-005
环境管理物质标准规范

包装图

Note注解:

1.Quantity数量:

5K PCS/REEL 一卷5KPCS ; 9 REEL/BOX 一箱9卷 ; 45K PCS/BOX 一箱45KPCS

2.Each reel and outer box must be labeled and Eco-Label Respectively labeled

每盘和外箱都必须有标签及环保标签分别标示

3.Terminal winding direction as shown端子缠绕方向如左图所示

4.There shall be no dirt such as deformation phenomenon,Mantissa box fillers must be used

每箱不可有脏污,变形现象,尾数箱必须用填充物

5.Carton material:K=K, Carton thickness:6~7mm纸箱材质:K=K, 纸箱厚度:6~7mm

6.One waterproof bag, two packets of desiccant 10g and four triangle guard plates should be placed in each carton

每箱里面要放一个防水袋和两包干燥剂10g及四个三角护板

7.Up and down "工" type sealing form

上下“工”字型封箱形式

Applicable Product No.
适用产品料号

2024TM-BSN1-X

Label face up
标签面朝上

Waterproof bag防水袋

Drier干燥剂放两包共10g

Label unified on the
box top right corner
外箱标签位于右上角Adhesive tape
胶带Four paper edge boards
四周放四个护角

卷装方式

Package way

						一般公差	SMS 东莞市思索技术股份有限公司 Dongguan SESO Technology Co.,Ltd.				料 号： PK-2024TM-BSN1-X				
						.X ±0.35					名 称： 2.00mm Terminal Packing				
						.XX ±0.25									
						.XXX ±0.15									
20220311	X0	/	首次发行	/	邹 洪	X ±2	核 准	审 查	制 作	日 期	单 位	比 例	页 次	版 本	编 号
日期	版次	变更编号	变更内容说明	变更人	核 准		邹 洪	赵 才	滕 敏	2022/03/11	mm	1:1	1/1	A0	A-XXX

RoHS

本产品符合我司QA-3-04-005
环境管理物质标准规范

包装图

240mm Min
后空10穴

7200mm (Quantity包装数量:300PCS)


240mm Min
前空10穴

热封上带
Heatsealing

Axes

Total length of carrier tape载带总长度:7680mm

Reserved top tape 320mm
预留上带320mm



ø380

ø13

Discharge direction 拉出方向

Receiving direction
收料方向

Label 标签

Single hole: None hole side

Double hole: Elliptical hole side


双孔: 贴椭圆孔侧

Vacuum packing

真空包装

Drier

干燥剂放2包5g



Material detail diagram
材料明细示意图

Cover tape peel strength:20~120g
剥离力量:20~120g

Peel speed:300mm/minute
剥离速度:300mm/minute

Peeling direction
剥离方向


Cover tape
上带

Carrier tape
下带


Pull out direction 拉出方向

Outer box 外箱


Label 标签




Four paper edge boards
四周放四个护角

20241115	A5	EN20241115001	Improve the carrier tape fool-proofing change its structure改善载带防呆, 变更载带的结构	Tim Teng 滕敏	Larry Yang 杨蒙	一般公差	SMS 东莞市思索技术股份有限公司 Dongguan SESO Technology Co.,Ltd.				料号: PK-2024WVS-2*XXX-LPXXXBR					
20221014	A4	EN120221014001	Change package material, color 变更包材材质、颜色	Tim Teng 滕敏	Larry Yang 杨蒙	.X ±0.35					名称: 2.00mm Connectors 180° Packing					
20220913	A3	EN120220913001	Change reel material, color 变更卷盘材质、颜色	Tim Teng 滕敏	Larry Yang 杨蒙	.XX ±0.25										
						.XXX ±0.15										
						X: ±Z										
日期	版次	变更编号	变更内容说明	变更人	核准	视角 	核准	邹洪	赵才	滕敏	2021/07/14	单位	比例	页次	版本	编号
												mm	1:1	1/2	A5	A-370

Carrier Tape No. 载带料号	B0	W	S	F	T	G	REEL PCS/卷	CARTON R/箱	CARTON PCS/箱
ZD2024WVS-2*02HF-C	11.60								
ZD2024WVS-2*03HF-C	13.60	32	28.40	14.20	36.5	32.5	300	9	2700
ZD2024WVS-2*04HF-C	15.60								
ZD2024WVS-2*05HF-C	17.60								
ZD2024WVS-2*06HF-C	19.60								
ZD2024WVS-2*07HF-C	21.60	44	40.40	20.20	48.5	44.5	300	7	2100
ZD2024WVS-2*08HF-C	23.60								
ZD2024WVS-2*09HF-C	25.60								
ZD2024WVS-2*10HF-C	27.60								
ZD2024WVS-2*11HF-C	29.60								
ZD2024WVS-2*12HF-C	31.60								
ZD2024WVS-2*13HF-C	33.60	56	52.40	26.20	60.5	56.5	300	5	1500
ZD2024WVS-2*14HF-C	35.60								
ZD2024WVS-2*15HF-C	37.60								
ZD2024WVS-2*16HF-C	39.60								
ZD2024WVS-2*17HF-C	41.60								
ZD2024WVS-2*18HF-C	43.60	72	68.40	34.20	76.5	72.5	300	4	1200
ZD2024WVS-2*19HF-C	45.60								
ZD2024WVS-2*20HF-C	47.60								




- Note:
- Carrier Camber Is Within 1mm In 100mm ; 带长100mm内容许弯曲度1mm
 - 10 Sprocket Hole Pitch Cumulative Tolerance±0.2MM ; 圆孔十个孔距离累计允许公差为±0.2mm
 - Carrier tape material: Halogen-Free PS,thickness=0.50±0.05mm,color:lucency.
载带材质:无卤PS,厚度=0.50±0.05mm,颜色:透明色.
 - Bracer material: Halogen-Free PS,thickness=0.40±0.05mm,color:lucency.
保护带材质:无卤PS,厚度=0.40±0.05mm,颜色:透明色.
 - Cover tape material: Halogen-Free PET,Heat sealing (lucency)
上带材质:无卤PET,热封(透明色)
 - Reel material: Halogen-Free PS,color:blue.卷盘材质:无卤PS,颜色:蓝色.
 - Carton material纸箱材质:K=K; Carton Thickness纸箱厚度: 6~7mm
 - Standard for durability of carton:average 14Kgf/cm²minimum; 纸箱耐破力标准: 平均14Kgf/cm²最小
 - Standard for compressive strength of carton:400Kgf minimum; 纸箱抗压强度标准: 400Kgf最小



Applicable Product No. 适用产品料号	2024WVS-2*XX-LPXXXBR
	2024WVS-2*XXY-LPXXXBR

20241115	A5	EN20241115001	Improve the carrier tape fool-proofing change its structure改善载带防呆, 变更载带的结构	Lim Teng 滕敏	Larry Yang 杨蒙	一般公差	料号: PK-2024WVS-2*XXX-LPXXXBR
20221014	A4	EN120221014001	Change package material,color 变更包材材质、颜色	Lim Teng 滕敏	Larry Yang 杨蒙	.X ±0.35	名称: 2.00mm Connectors 180° Packing
20220913	A3	EN120220913001	Change reel material,color 变更卷盘材质、颜色	Lim Teng 滕敏	Larry Yang 杨蒙	.XX ±0.25	单位 比例 页次 版本 编号
						.XXX ±0.15	mm 1:1 2/2 A5 A-370
日期	版次	变更编号	变更内容说明	变更人	核准	X: ±2	
						视图	



20221014	A4	EN120221014001	Change package material, color 变更包材材质、颜色	Tim Teng 滕敏	Larry Yang 杨莹	一般公差 .X ±0.35	SMS 东莞市思索技术股份有限公司 Dongguan SESO Technology Co.,Ltd.				料 号： PK-2024WRS-2*XXX-LPXXXBR								
20220913	A3	EN120220913001	Change reel material, color 变更卷盘材质、颜色	Tim Teng 滕敏	Larry Yang 杨莹	.XX ±0.25					核 准 审 查 制 作 日 期				名 称： 2.00mm Connectors 90° Packing				
20220429	A2	EN120220429001	Change reel material, color 变更卷盘材质、颜色	Tim Teng 滕敏	Larry Yang 杨莹	.XXX ±0.15									邹 洪 赵 才 滕 敏 2021/07/14				单位 比例 页次 版本 编号
日期	版次	变更编号	变更内容说明	变更人	核 准	视 角					mm 1:1 1/2 A4 A-370								

RoHS


本产品符合我司QA-3-04-005
环境管理物质标准规范

包装图

Carrier Tape No. 载带料号	W	S	F	T	G	REEL 卷/PCS	CARTON 箱/R	CARTON 箱/PCS
ZD2024WRS-2*02HF-C	32.0	28.40	14.20	36.5	32.5	450	9	4050
ZD2024WRS-2*03HF-C								
ZD2024WRS-2*04HF-C								
ZD2024WRS-2*05HF-C	44.0	40.40	20.20	48.5	44.5	450	7	3150
ZD2024WRS-2*06HF-C								
ZD2024WRS-2*07HF-C								
ZD2024WRS-2*08HF-C								
ZD2024WRS-2*09HF-C	56.0	52.40	26.20	60.5	56.5	450	5	2250
ZD2024WRS-2*10HF-C								
ZD2024WRS-2*11HF-C								
ZD2024WRS-2*12HF-C								
ZD2024WRS-2*13HF-C								
ZD2024WRS-2*14HF-C	72.0	68.40	34.20	76.5	72.5	450	4	1800
ZD2024WRS-2*15HF-C								
ZD2024WRS-2*16HF-C								
ZD2024WRS-2*17HF-C								
ZD2024WRS-2*18HF-C								
ZD2024WRS-2*19HF-C								
ZD2024WRS-2*20HF-C								

Note:

- Carrier Camber Is Within 1mm In 100mm ; 带长100mm内容许弯曲度1mm
- 10 Sprocket Hole Pitch Cumulative Tolerance ± 0.2 MM ; 圆孔十个孔距离累计允许公差为 ± 0.2 mm
- Carrier tape material: Halogen-Free PS,thickness=0.50 ± 0.05 mm,color:lucency.
载带材质:无卤PS,厚度=0.50 ± 0.05 mm,颜色:透明色. 
- Bracer material: Halogen-Free PS,thickness=0.40 ± 0.05 mm,color:lucency.
保护带材质:无卤PS,厚度=0.40 ± 0.05 mm,颜色:透明色. 
- Cover tape material: Halogen-Free PET,Heat sealing (lucency)
上带材质:无卤PET,热封(透明色) 
- Reel material: Halogen-Free PS,color:blue.卷盘材质:无卤PS,颜色:蓝色. 
- Carton material纸箱材质:K=K; Carton Thickness纸箱厚度: 6~7mm
- Standard for durability of carton:average 14Kgf/cm²minimum; 纸箱耐破力标准: 平均14Kgf/cm²最小
- Standard for compressive strength of carton:400Kgf minimum; 纸箱抗压强度标准: 400Kgf最小

Applicable Product No.
适用产品料号2024WRS-2*XX-LPXXXBR
2024WRS-2*XXY-LPXXXBR

20221014	A4	EN120221014001	Change package material, color 变更包材材质、颜色	Tim Teng 滕敏	Larry Yang 杨棠	一般公差	 东莞市思索技术股份有限公司 Dongguan SESO Technology Co., Ltd.				料号: PK-2024WRS-2*XXX-LPXXXBR 名称: 2.00mm Connectors 90° Packing				
20220913	A3	EN120220913001	Change reel material, color 变更卷盘材质、颜色	Tim Teng 滕敏	Larry Yang 杨棠	.X ± 0.35 .XX ± 0.25 .XXX ± 0.15 X: ± 2									
20220429	A2	EN120220429001	Change reel material, color 变更卷盘材质、颜色	Tim Teng 滕敏	Larry Yang 杨棠	视角									
日期	版次	变更编号	变更内容说明	变更人	核准	审核	核准	审查	制作	日期	单位	比例	页次	版本	编号
							邹洪	赵才	滕敏	2021/07/14	mm	1:1	2/2	A4	A-370